

# HEPA NVR170H

Advanced HEPA13 Filtration



**Increase cleaning & hygiene standards with advanced HEPA13 filtration.**

- ✓ Great Features for the Toughest Cleaning
- ✓ Advanced HEPA13 Filtration
- ✓ What Goes in, Stays in




**Numatic**

## Advanced HEPA13 Filtration

Delivering certified HEPA13 standards typically demanded in Healthcare environments of filtration down to 0.3 microns at 99.97% efficiency.

The HEPA13 filter cartridge captures and traps fine particles, such as pollen, dust mites and pathogens, including bacteria, reducing the risk of recirculation of these particles back into the environment.



High-efficiency, pleated glass media construction.




### HEPA Filter

Certified HEPA13 filtration down to 0.3 microns at 99.97% efficiency. Our most advanced filtration in the Numatic commercial vacuum series.



### Powerful Motor

Tested for a minimum of 1600 hours' continuous life, delivering powerful, efficient and long-life cleaning performance.



### 3-Stage Filtration

Advanced, 3-stage filtration system cleans and traps fine dust, including allergy triggers and pathogens, eliminating the risk of recirculation and exposure.

### TriTex Filter

Traps fine dust within its high-efficiency, triple-layer membrane.



### HepaFlo Filter Bag

3-layers of high-efficiency filter material and unique self-seal tab trap and retain fine dust during vacuuming and emptying.

### Built to Last

Tested beyond industry standards, delivering performance you can trust from the UK's most reliable vacuum brand.



On-board Tool Storage

## Kit AS32



## Numatic HEPA Range



For further information visit [numatic.co.uk](http://numatic.co.uk)

Model	Capacity	Power Cord	Motor	Weight	Power	Cleaning Range	Suction H20	Airflow	Filtration Class	Dimensions (WxLxH)	Kit
NVR170H	7.2L	10m	620W	8.2kg	230V AC 50/60Hz	26.4m	2300mm	48L / sec	Type H13 (EN1822)	360x370x390mm	AS32